

### Characteristics



Pharma Applications



Dry Recovery




Cleanroom Compatible



ULPA Filter Available

ULPA - Optional



HEPA Filter Available

HEPA - Optional



Continuous Duty



- HEPA filter with an efficiency of 99.995% at 0.3 micron. Tested IEST-RP-CC001. H14 by MPPS method as per EN 1822 and OSHA compliant. All of our HEPA vacuum systems are aerosol leak tested before leaving our facility - optional
- ULPA filter with an efficiency of 99.999% at 0.12 micron. Filtration efficiency of 99.9995% at 0.18 micron. Tested IEST-RP-CC001. U15 by MPPS method as per EN 1822. All of our ULPA vacuum systems are aerosol leak tested before leaving our facility - optional
- Cleanroom compatible with ISO Class 4 (former Class 10)
- Designed to be attached to process machines and for general cleanup in the Food industry
- Can also be used for the recovery of tablets in the Pharmaceutical industry
- Continuous duty single phase or 3-phase motor mounted vertically
- Available in a fixed or mobile unit
- For dry recovery only
- Available in stainless steel, white powder coated or stainless steel & white powder coated versions
- Vertical mounting for areas with space constraints
- 4 wheels for easy maneuverability

## Specifications

CD-1501 CR (STD) SERIES	110984B1	110984B3	110986B1	110986B3
<b>Model Name</b>	CD-1501 CR (STD) - P/C & S/S	CD-1501 CR (STD) - P/C & S/S	CD-1501 CR (STD) - STAINLESS STEEL	CD-1501 CR (STD) - STAINLESS STEEL
<b>Type (Powerhead)</b>	Electric	Electric	Electric	Electric
<b>TEFC Motor</b>	Yes	Yes	Yes	Yes
<b>Tension</b>	230 V	400 V	230 V	400 V
<b>Frequency</b>	50 Hz	50 Hz	50 Hz	50 Hz
<b>Phase</b>	Single	Three	Single	Three
<b>Wattage</b>	1750 W	1750 W	1750 W	1750 W
<b>Power</b>	1.7 kW	1.7 kW	1.7 kW	1.7 kW
<b>Amperage</b>	9 A	3 A	9 A	3 A
<b>Air Flow</b>	238 m <sup>3</sup> /h	238 m <sup>3</sup> /h	238 m <sup>3</sup> /h	238 m <sup>3</sup> /h
<b>Vacuum Pressure</b>	2820+ mm H <sub>2</sub> O	2820+ mm H <sub>2</sub> O	2820+ mm H <sub>2</sub> O	2820+ mm H <sub>2</sub> O
<b>VRV Setting</b>	2795 mm H <sub>2</sub> O	2795 mm H <sub>2</sub> O	2795 mm H <sub>2</sub> O	2795 mm H <sub>2</sub> O
<b>Sound Level</b>	64 dB(A)	64 dB(A)	64 dB(A)	64 dB(A)
<b>Type of Power Outlet</b>	Not Included	Not Included	Not Included	Not Included
<b>Suction Inlet Port</b>	50 mm	50 mm	50 mm	50 mm
<b>Cart Type</b>	Carriage Base (CB)	Carriage Base (CB)	Carriage Base (CB)	Carriage Base (CB)
<b>Filter Cleaning</b>	None	None	None	None
<b>Dust Recovery Tank</b>	28.4 L	28.4 L	28.4 L	28.4 L
<b>Dry Recovery - Disposable Filter Bag</b>	15 L	15 L	15 L	15 L
<b>Length</b>	34 cm	34 cm	34 cm	34 cm
<b>Width</b>	50 cm	50 cm	50 cm	50 cm
<b>Height</b>	109 cm	109 cm	109 cm	109 cm
<b>Weight (Vacuum Only)</b>	51.5 kg.	51.5 kg.	51.5 kg.	51.5 kg.
<b>Cord Length</b>	10 m	10 m	10 m	10 m

Please note that specifications are subject to change without notice

### Use only recommended tools & accessories



Tools and Accessories (Toolkit 4B) - Optional